

# Arc® 36 HC

## Chambers



Arc 36 HC

Leaching chambers are rapidly becoming the product of choice for leachfield applications over conventional pipe and gravel systems. Their lightweight construction offers lower installed costs and less intrusive installations.



The Arc 36 High Capacity (HC) septic chamber is a sturdy, lightweight plastic unit that combines maximized infiltrative surface area and storage capacity with an improved structural design to handle most any conventional leachfield system challenge without sacrificing performance.

### Benefits

- Injection-molded from polyolefin for lightweight and sturdy design.
- 10-degree integral articulating joint that is ideal for either straight or contoured septic leachfield applications.
- Corrugated chamber design eliminates flat surfaces and provides increased load bearing capability in the trench
- Designed to accommodate both gravity-fed and pressure-dosed systems.
- "Lock and Drop" joint provides a more positive connection during installation and backfill.
- A universal inlet/outlet endcap.
- Inspection/vent ports on each chamber with easy-to-remove knockouts for maximum job site flexibility.
- Convenient five-foot lengths are easy to handle.
- Quickly installed by one person into three-foot wide trench or bed applications.
- Increased inletting options with Side Port Coupler component which snaps in place to allow side entry at any joint throughout trench line.
- Diamond plate texture increases slip resistance and enhances ease of installation.

### Arc 36 HC CHAMBER

Length	63" (1,600 mm)
Repeat Length	60" (1,524 mm)
Sidewall Height	10.75" (273 mm)
Overall Height	16" (406 mm)
Overall Width	34" (876 mm)
Weight	17 lbs
Total Bottom Area	12.27 sq ft
Capacity	10.5 cu ft (78.5 gal)



### CHAMBER REQUIREMENTS

Chamber shall meet the load rating of H-10 (16,000 lb per axle) with a minimum of 12 inches of cover when tested in accordance with IAPMO PS 63 and installed in accordance with manufacturers installation procedures.

### CHAMBER CONNECTION

Each chamber shall interlock with an integral articulating joint. Articulating joints shall have a free range of horizontal rotation of 20 degrees, with a maximum of 10 degrees in either direction. Articulating joint shall be constructed by placing the dome with previously-installed chamber, with final engagement occurring when the lower base flanges of the incoming chamber under-lap the raised base flanges of the previously-installed chamber.

Contact Infiltrator's Technical Services Department  
for assistance at 1-800-221-4436  
or [info@infiltratorwater.com](mailto:info@infiltratorwater.com)



**Infiltrator**  
Water Technologies  
Part of **ADS**